

Specification Sheet

Part Number: 126-00099



All-in-one bundling and mounting solution reduces costs.

Low-profile design provides dependable cable management in tight spaces.

1-Piece Cable Tie with Fir Tree Mount, 6.1" Long, 0.19 - 0.21" Mounting Hole Diameter, PA66HS, Black, 1000/pkg

Article Number	126-00099
Type	T50SOSKSFT5S-E
Color	Black (BK)
Quantity Per	pack
Product Description	The low-profile push mount design provides an overall shortened length, which assists in limiting protrusion on the opposing side of application surfaces. The mount’s rounded tip allows for a smoother surface in case of contact with surrounding components or hands. The dome provides firm, rattle-free performance and keeps out debris. One-piece mounting ties offer a complete solution by both bundling and mounting.
Short Description	1-Piece Cable Tie with Fir Tree Mount, 6.1" Long, 0.19 - 0.21" Mounting Hole Diameter, PA66HS, Black, 1000/pkg

Global Part Name	T50SOSKSFT5S-E-PA66HS-BK
------------------	--------------------------

Minimum Tensile Strength (Imperial)	40
-------------------------------------	----

Minimum Tensile Strength (Metric)	180
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	156.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.04
--------------------------------	------

Bundle Diameter Min (Metric)	1.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.05
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	1.3
Mounting Hole Diameter D (Imperial)	0.19 - 0.2
Mounting Hole Diameter D (Metric)	4.8 - 5.2 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.2
Mounting Hole Diameter D Max (Metric)	5.2
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Minimum Extraction Force (Imperial)	40.0
Minimum Extraction Force (Metric)	180
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)