

Specification Sheet

Part Number: 126-00049



- One piece assembly allows the mount to slide along the strap ensuring proper orientation.
- Arrowhead style mount provides low insertion and high extraction force.
- Arrowhead disc protects against dirt and other impurities.

1-Piece Cable Tie with Arrowhead Mount with Wings, 6"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HIRHSUV, Black, 500/bg

Article Number	126-00049
Type	T50SSFMT
Color	Black (BK)
Quantity Per	pack
Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
Short Description	1-Piece Cable Tie with Arrowhead Mount with Wings, 6"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HIRHSUV, Black, 500/bg

Global Part Name	T50SSFM-PA66HIRHSUV-BK
------------------	------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	6.3
---------------------	-----

Length L (Metric)	160.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.13
--------------------------------	------

Bundle Diameter Min (Metric)	3.2
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Height H (Imperial)	0.20
Height H (Metric)	5.60
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.0 - 6.6 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.6
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)