

Specification Sheet

Part Number: 126-00065

Design helps silence and stabilize the tie in high-vibration applications.



Arrowhead-style mount provides low insertion and high extraction force.

Rubber seal restricts water and debris from passing through mounting hole.

1-Piece Cable Tie with Arrowhead Mount with Seal, 6.5" Long, 50lb Tensile, PA66HS, Natural, 500/bg

Article Number

126-00065

Type

T50SOSSFT6.5E-MS-MD

Color

Natural (NA)

Quantity Per

pack

Product Description

The arrowhead design of these ties offers a positive, low insertion force and a high extraction force. These ties feature a foam rubber seal which provides additional protection against moisture, dirt, and other impurities. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description

1-Piece Cable Tie with Arrowhead Mount with Seal, 6.5" Long, 50lb Tensile, PA66HS, Natural, 500/bg

Global Part Name	T50SOSSFT6.5E-MS-MD-PA66HS-NA
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	40
-------------------------------------	----

Minimum Tensile Strength (Metric)	180
-----------------------------------	-----

Length L (Imperial)	6.5
---------------------	-----

Length L (Metric)	163.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Height H (Imperial)	0.63
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.06
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	1.6
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 " (HEXAGONAL) 0.25 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.6 mm (hexagonal) 6.25 - 6.75 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.75
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)