

Specification Sheet

Part Number: 126-00080

- Design helps silence and stabilize the tie in high-vibration applications.
- Arrowhead-style mount provides low insertion and high extraction force.
- Anti-rotational oval fastener forces bundle to travel in intended direction.
- Rubber seal restricts water and debris from passing through mounting hole.



Article Number	126-00080
Type	T60SOSSFT62x122-E-MD
Color	Black (BK)
Quantity Per	pack
Product Description	Push Mount Ties with Seal for Oval Holes provide a one-piece bundling and mounting solution. The oval arrowhead fastener won't rotate once inserted into a panel hole, ensuring proper routing of wires and hoses. The welded rubber seal protects against the ingress of water and debris.
Short Description	1-Piece Cable Tie with Oval Arrowhead Mount with Seal, 6.2" Long, Mounting Hole Diameter 0.24 x 0.48", PA66HS, Black, 500/pkg
Global Part Name	T60SOSSFT62x122-E-MD-PA66HS-BK

Minimum Tensile Strength (Imperial)	67
Minimum Tensile Strength (Metric)	300
Length L (Imperial)	6.2
Length L (Metric)	157.5
Fixation Method	Arrowhead for oval holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.22
Width W (Metric)	5.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30.0
Thickness T (Metric)	1.35

Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 "
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.48
Mounting Hole Diameter D Max (Metric)	12.2
Disc Diameter (Metric)	16.0 x 22.0
Disc Diameter (Imperial)	0.63 x 0.87
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)