

Specification Sheet

Part Number: 126-00116



Wing design helps stabilize the tie in high-vibration applications.

Includes a ladder-type strap as opposed to a conventional serrated strap which provides the benefit of being extra flexible.

1-Piece Cable Tie with Arrowhead Mount with Wings, 8"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HS, Black, 500/bg

Article Number	126-00116
Type	T50RSFM
Color	Black (BK)
Quantity Per	pack
Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
Short Description	1-Piece Cable Tie with Arrowhead Mount with Wings, 8"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HS, Black, 500/bg

Global Part Name	T50RSFM-PA66HS-BK
------------------	-------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.77
--------------------------------	------

Bundle Diameter Max (Metric)	45.0
------------------------------	------

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Height H (Imperial)	.22
Height H (Metric)	5.59
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.0 - 6.6 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.6
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com