

Specification Sheet

Part Number: 126-00186

- Design helps silence and stabilize the tie in high-vibration applications.
- Arrowhead-style mount provides low insertion and high extraction force.
- Anti-rotational oval fastener forces bundle to travel in intended direction.
- Rubber seal restricts water and debris from passing through mounting hole.



Push Mount Tie with Seal, 6.2" Long, Mounting Hole Diameter 0.26 x 0.51", PA66HS, Black, 500/pkg

Article Number	126-00186
Type	T60SOSSFT65x130-E-MS-MD
Color	Black (BK)
Quantity Per	pack
Product Description	Push Mount Ties with Seal for Oval Holes provide a one-piece bundling and mounting solution. The oval arrowhead fastener won't rotate once inserted into a panel hole, ensuring proper routing of wires and hoses. The welded rubber seal protects against the ingress of water and debris.
Short Description	Push Mount Tie with Seal, 6.2" Long, Mounting Hole Diameter 0.26 x 0.51", PA66HS, Black, 500/pkg

Global Part Name	T60SOSSFT65x130-E-MS-MD-PA66HS-BK
------------------	-----------------------------------

Minimum Tensile Strength (Imperial)	67
-------------------------------------	----

Minimum Tensile Strength (Metric)	300
-----------------------------------	-----

Length L (Imperial)	6.2
---------------------	-----

Length L (Metric)	158.0
-------------------	-------

Fixation Method	Arrowhead for oval holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.22
--------------------	------

Width W (Metric)	5.5
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	1.18
--------------------------------	------

Bundle Diameter Max (Metric)	30.0
------------------------------	------

Thickness T (Metric)	1.35
----------------------	------

Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.26 - 0.51 "
Mounting Hole Diameter D (Metric)	6.5 x 13.0 mm
Mounting Hole Diameter D Min (Imperial)	0.26
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0
Disc Diameter (Metric)	16.0 x 22.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)