

## Specification Sheet

Part Number: 126-00326



All-in-one bundling and mounting solution reduces costs.

Disc provides a tight, rattle-free installation.

Low-profile design provides dependable cable management in tight spaces.

1-Piece Cable Tie with Arrowhead Mount with Disc, 6.0"L, 0.25 - 0.26" Mounting Hole, PA66HS, Black, 500/pkg

|                     |                                                                                                                                                                                                                                                                                                                  |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 126-00326                                                                                                                                                                                                                                                                                                        |
| Type                | T50SOSKSFT6.5S2-E                                                                                                                                                                                                                                                                                                |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                       |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                             |
| Product Description | HellermannTyton's low profile push mount design provides an overall shortened length which assists in limiting protrusion on the opposing side of application surfaces. The rounded tip of the mount allows for a smoother surface in case of contact with surrounding components or human touch during service. |
| Short Description   | 1-Piece Cable Tie with Arrowhead Mount with Disc, 6.0"L, 0.25 - 0.26" Mounting Hole, PA66HS, Black, 500/pkg                                                                                                                                                                                                      |
| Global Part Name    | T50SOSKSFT6.5S2-E-PA66HS-BK                                                                                                                                                                                                                                                                                      |

|                                     |                  |
|-------------------------------------|------------------|
| Minimum Tensile Strength (Imperial) | 50               |
| Minimum Tensile Strength (Metric)   | 225              |
| Length L (Imperial)                 | 6.0              |
| Length L (Metric)                   | 157.0            |
| Fixation Method                     | Arrowhead        |
| Identification Plate Position       | none             |
| Releasable Closure                  | No               |
| Tie Closure                         | plastic pawl     |
| Variant                             | Outside Serrated |
| Width W (Imperial)                  | 0.18             |
| Width W (Metric)                    | 4.6              |
| Bundle Diameter Min (Imperial)      | 0.04             |
| Bundle Diameter Min (Metric)        | 1.0              |
| Bundle Diameter Max (Imperial)      | 1.38             |
| Bundle Diameter Max (Metric)        | 35.0             |
| Thickness T (Imperial)              | 0.05             |

|                                         |                                        |
|-----------------------------------------|----------------------------------------|
| Thickness T (Metric)                    | 1.3                                    |
| Height H (Imperial)                     | 0.58                                   |
| Height H (Metric)                       | 14.732                                 |
| Panel Thickness Min (Imperial)          | 0.07                                   |
| Panel Thickness Max (Imperial)          | 0.09                                   |
| Panel Thickness Min (Metric)            | 1.7                                    |
| Panel Thickness Max (Metric)            | 2.3                                    |
| Mounting Hole Diameter D (Imperial)     | 0.25 - 0.26 "                          |
| Mounting Hole Diameter D (Metric)       | 6.3 - 6.7 mm                           |
| Mounting Hole Diameter D Min (Imperial) | 0.25                                   |
| Mounting Hole Diameter D Max (Imperial) | 0.26                                   |
| Mounting Hole Diameter D Max (Metric)   | 6.7                                    |
| Disc Diameter (Metric)                  | 16.0                                   |
| Disc Diameter (Imperial)                | 0.63                                   |
| Material                                | Polyamide 6.6 heat stabilized (PA66HS) |

|                              |                                   |
|------------------------------|-----------------------------------|
| Material Shortcut            | PA66HS                            |
| Flammability                 | UL 94 V-2                         |
| UV Resistant (Yes/No)        | No                                |
| Use Conditions               | For Indoor and Outdoor Use        |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| Package Quantity (Imperial)  | 500                               |
| Package Quantity (Metric)    | 500                               |
| Customs Number               | 3926909988                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)