

Specification Sheet

Part Number: T30RSF0M4



All-in-one bundling and fastening solution reduces costs and assembly time.

The arrowhead design of these ties offers a low insertion force and a high extraction force.

High-spec materials and superior design deliver versatility, performance and value.

1-Piece Cable Tie with Arrowhead Mount, 6.3"L, 30lb, 0.04 - 0.09" Panel Thickness, PA66HS, Black, 1000/pkg

|                     |                                                                                                                                                                                                                                                                                                                                                                                  |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 126-00702                                                                                                                                                                                                                                                                                                                                                                        |
| Type                | T30RSF(U)                                                                                                                                                                                                                                                                                                                                                                        |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                                                       |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                                             |
| Product Description | One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications. |
| Short Description   | 1-Piece Cable Tie with Arrowhead Mount, 6.3"L, 30lb, 0.04 - 0.09" Panel Thickness, PA66HS, Black, 1000/pkg                                                                                                                                                                                                                                                                       |

|                  |                     |
|------------------|---------------------|
| Global Part Name | T30RSF(U)-PA66HS-BK |
|------------------|---------------------|

|                                     |    |
|-------------------------------------|----|
| Minimum Tensile Strength (Imperial) | 30 |
|-------------------------------------|----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 135 |
|-----------------------------------|-----|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 6.3 |
|---------------------|-----|

|                   |        |
|-------------------|--------|
| Length L (Metric) | 160.02 |
|-------------------|--------|

|                 |           |
|-----------------|-----------|
| Fixation Method | Arrowhead |
|-----------------|-----------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|                    |    |
|--------------------|----|
| Releasable Closure | No |
|--------------------|----|

|             |              |
|-------------|--------------|
| Tie Closure | plastic pawl |
|-------------|--------------|

|         |                 |
|---------|-----------------|
| Variant | Inside Serrated |
|---------|-----------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.14 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 3.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.06 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 1.6 |
|------------------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 1.22 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 31.0 |
|------------------------------|------|

|                                         |                                        |
|-----------------------------------------|----------------------------------------|
| Thickness T (Imperial)                  | 0.05                                   |
| Thickness T (Metric)                    | 1.2                                    |
| Height H (Imperial)                     | .20                                    |
| Height H (Metric)                       | 5.70                                   |
| Panel Thickness Min (Imperial)          | 0.04                                   |
| Panel Thickness Max (Imperial)          | 0.09                                   |
| Panel Thickness Min (Metric)            | 0.9                                    |
| Panel Thickness Max (Metric)            | 2.4                                    |
| Mounting Hole Diameter D (Imperial)     | 0.19 - 0.22 "                          |
| Mounting Hole Diameter D (Metric)       | 4.7 - 5.6 mm                           |
| Mounting Hole Diameter D Min (Imperial) | 0.19                                   |
| Mounting Hole Diameter D Max (Imperial) | 0.22                                   |
| Mounting Hole Diameter D Max (Metric)   | 5.6                                    |
| Material                                | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut                       | PA66HS                                 |

|                               |                                   |
|-------------------------------|-----------------------------------|
| Flammability                  | UL 94 V-2                         |
| UV Resistant (Yes/No)         | No                                |
| Use Conditions                | For Indoor and Outdoor Use        |
| Operating Temperature         | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33)  | Yes                               |
| ROHS Compliant                | Yes                               |
| Certification/Specification   | UL-ZODZ2.E64139                   |
| UL Recognized (US)            | Yes                               |
| UL Recognized (US and Canada) | Yes                               |
| Package Quantity (Imperial)   | 1000                              |
| Package Quantity (Metric)     | 1000                              |
| Customs Number                | 3926909988                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)