

Specification Sheet

Part Number: T50RSF9M4



All-in-one bundling and fastening solution reduces costs and assembly time.

The arrowhead design of these ties offers a low insertion force and a high extraction force.

High-spec materials and superior design deliver versatility, performance and value.

1-Piece Cable Tie with Arrowhead Mount, 8.3"L, 50lb, 0.04 - 0.14" Panel Thickness, PA66, Natural, 1000/pkg

Article Number	126-01011
Type	T50RSF(U)
Color	Natural (NA)
Quantity Per	pack
Product Description	One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications.
Short Description	1-Piece Cable Tie with Arrowhead Mount, 8.3"L, 50lb, 0.04 - 0.14" Panel Thickness, PA66, Natural, 1000/pkg

Global Part Name	T50RSF(U)-PA66-NA
------------------	-------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.3
---------------------	-----

Length L (Metric)	210.82
-------------------	--------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	1.75
--------------------------------	------

Bundle Diameter Max (Metric)	44.5
------------------------------	------

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	.30
Height H (Metric)	7.50
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.14
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.56
Mounting Hole Diameter D (Imperial)	0.25 - 0.28 "
Mounting Hole Diameter D (Metric)	6.4 - 7.1 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.1

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com