

Specification Sheet

Part Number: 126-02204

Arrowhead design makes installation by hand quick and easy without the need for tools.

Ties "clicks" into place upon final installation signaling installer insertion is complete.

Design provides low insertion and high extraction force.



1-Piece Cable Tie with Arrowhead Mount with Wings, 5.3"L, 50lb, 0.24 - 026" Hole Dia, PA66HIRHS, Black, 500/bg

Article Number	126-02204
Type	T50SSL5
Color	Black (BK)
Quantity Per	pack
Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
Short Description	1-Piece Cable Tie with Arrowhead Mount with Wings, 5.3"L, 50lb, 0.24 - 026" Hole Dia, PA66HIRHS, Black, 500/bg

Global Part Name	T50SSL5-PA66HS-BK
------------------	-------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	5.3
---------------------	-----

Length L (Metric)	135
-------------------	-----

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.06
--------------------------------	------

Bundle Diameter Max (Metric)	27.0
------------------------------	------

Height H (Imperial)	0.4
Height H (Metric)	10
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.11
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	2.7
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.1 - 6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.5
Disc Diameter (Imperial)	0.64

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)