

Specification Sheet

Part Number: GTM500C2



Non adhesive with 1/4" screw hole mount secures .5" grip ties for use on flat surfaces

Article Number	130-95000
Type	GTM50
Color	Black (BK)
Quantity Per	pack
Product Description	To secure bundles to flat surfaces, HellermannTyton offers a mounting base to be used with the Grip Ties. Available with or without adhesive, two sizes of Grip Tie mounts cover every size of Grip Tie. The mounts are manufactured from nylon 6/6 material and are UV-stabilized for outdoor applications.
Short Description	Grip Tie Mount for 0.5" Wide Grip Tie, Without Adhesive, PA66UV, Black, 100/pkg
Global Part Name	GTM50-PA66UV-BK

Length L (Imperial)	2.5
Length L (Metric)	63.5
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	hook and loop
Variant	Grip Tie
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bolt Size	1/4"
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.35 mm
Material	Polyamide 6.6 UV-stabilized (PA66UV)
Material Shortcut	PA66UV
UV Resistant (Yes/No)	Yes

Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)