

Specification Sheet

Part Number: 133-03836



Fir tree design provides low insertion force and high extraction force ideal for simple, secure performance in a 6.5 mm (+/-0.4) hole.

Standoff design secures the bundle away from the mounting hole and areas that could cause damage due to rubbing.

Clip can be installed by hand – no need for hardware or tools.

Standoff Bundling Clip, 1.4" Long, Panel Thickness 0.02 - 0.19mm, PA66HIRHS, Black, 1500/ctn

Article Number	133-03836
----------------	-----------

Type	SOC23SO18
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
---------------------	---

Short Description	Standoff Bundling Clip, 1.4" Long, Panel Thickness 0.02 - 0.19mm, PA66HIRHS, Black, 1500/ctn
-------------------	--

Global Part Name	SOC23SO18-PA66HIRHS-BK
------------------	------------------------

Length L (Imperial)	2.04
---------------------	------

Length L (Metric)	50.0
-------------------	------

Offset Length (Imperial)	0.889
--------------------------	-------

Offset Length (Metric)	22.6
------------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	1.4
--------------------	-----

Width W (Metric)	35.56
------------------	-------

Height H (Imperial)	1.2
---------------------	-----

Height H (Metric)	31.2
-------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.19
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	4.7
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial) 0.24

Mounting Hole Diameter D Max (Imperial) 0.27

Mounting Hole Diameter D Max (Metric) 6.9

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +230°F (-40°C to +110°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 1500

Package Quantity (Metric) 1500

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)