

Specification Sheet

Part Number: 133-01497



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 1.73" Long, Panel Thickness 0.02–0.27", PA66HIRHS, Natural, 2000/carton

Article Number	133-01497
----------------	-----------

Type	SOC14FT6
------	----------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.
---------------------	---

Short Description	Standoff Bundling Clip, 1.73" Long, Panel Thickness 0.02–0.27", PA66HIRHS, Natural, 2000/carton
-------------------	---

Global Part Name	SOC14FT6-PA66HIRHS-NA
------------------	-----------------------

Length L (Imperial)	1.77
---------------------	------

Length L (Metric)	45.0
-------------------	------

Offset Length (Imperial)	0.80
--------------------------	------

Offset Length (Metric)	20.3
------------------------	------

Fixation Method	Fir Tree
-----------------	----------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.24
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	6.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.24
---	------

Mounting Hole Diameter D Max (Imperial)	0.27
---	------

Mounting Hole Diameter D Max (Metric)	6.9
---------------------------------------	-----

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com