

Specification Sheet

Part Number: 133-03053



- Can be easily assembled to convoluted tubing and reliably remain in position
- Internal rib prevents movement or rattling
- Multiple configurations to mount to a variety of surfaces
- Releaseable to allow for maintenance

Conduit Clamps, Size 9, Mounting Hole 6.35 mm, Fir Tree, PP, Black, 800/pkg

|                     |                                                                                                                                                                                                                                                                                                                                             |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 133-03053                                                                                                                                                                                                                                                                                                                                   |
| Type                | CDC9FT6.35                                                                                                                                                                                                                                                                                                                                  |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                  |
| Quantity Per        | carton                                                                                                                                                                                                                                                                                                                                      |
| Product Description | The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Convoluted tubing clamps are available in various tubing diameters. Choose from arrowhead, fir tree, bundling clip, bracket and dual clamp configurations. |
| Short Description   | Conduit Clamps, Size 9, Mounting Hole 6.35 mm, Fir Tree, PP, Black, 800/pkg                                                                                                                                                                                                                                                                 |

|                  |                  |
|------------------|------------------|
| Global Part Name | CDC9FT6.35-PP-BK |
|------------------|------------------|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 2.51 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 63.8 |
|-------------------|------|

|                 |          |
|-----------------|----------|
| Fixation Method | Fir Tree |
|-----------------|----------|

|                    |     |
|--------------------|-----|
| Width W (Imperial) | 0.3 |
|--------------------|-----|

|                  |     |
|------------------|-----|
| Width W (Metric) | 8.2 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 0.35 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Max (Metric) | 9.0 |
|------------------------------|-----|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 1.94 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 49.3 |
|-------------------|------|

|                       |      |
|-----------------------|------|
| Diameter D (Imperial) | 0.42 |
|-----------------------|------|

|                     |      |
|---------------------|------|
| Diameter D (Metric) | 10.6 |
|---------------------|------|

|                                     |        |
|-------------------------------------|--------|
| Mounting Hole Diameter D (Imperial) | 0.25 " |
|-------------------------------------|--------|

|                                   |         |
|-----------------------------------|---------|
| Mounting Hole Diameter D (Metric) | 6.35 mm |
|-----------------------------------|---------|

|          |                    |
|----------|--------------------|
| Material | Polypropylene (PP) |
|----------|--------------------|

|                              |                                   |
|------------------------------|-----------------------------------|
| Material Shortcut            | PP                                |
| Flammability                 | UL 94 HB                          |
| Halogen Free                 | No                                |
| UV Resistant (Yes/No)        | No                                |
| Use Conditions               | For Indoor Use Only               |
| Operating Temperature        | -40°F to +239°F (-40°C to +115°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| Package Quantity (Imperial)  | 800                               |
| Package Quantity (Metric)    | 800                               |
| Customs Number               | 3926909988                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com