

Specification Sheet

Part Number: 133-03179



- Pipe clip secures routing to panel using a stud mount suited for a 5 or 6mm stud or bolt
- Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure
- Inverted retaining legs and narrow opening prevent inadvertent disengagement
- Controlled flex and angled entry promote easy installation

Tube and Pipe Clip with 5mm/6mm Stud Mount, 4.7-5.1mm Diameter, PA66HIRHSUV, Black, 5000/carton

Article Number	133-03179
Type	PC5SM6
Color	Black (BK)
Quantity Per	pack
Product Description	These clips can be attached to the stud prior to installing the pipe or hose. The parts prefixed with an 'I' can be interlocked together giving a greater choice of installation options or mounted onto a 5 mm 'T' stud or the IAHC type of Automatic Harness Clips.
Short Description	Tube and Pipe Clip with 5mm/6mm Stud Mount, 4.7-5.1mm Diameter, PA66HIRHSUV, Black, 5000/carton

Global Part Name	PC5SM6-PA66HIRHSUV-BK
Length L (Imperial)	0.39
Length L (Metric)	10.0
Fixation Method	Stud Mount
Width W (Imperial)	0.58
Width W (Metric)	14.73
Height H (Imperial)	0.59
Height H (Metric)	15.1
Nominal Diameter (Metric)	4.7
Mounting Hole Diameter D (Metric)	M6
Stud Diameter (Metric)	M6
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)