

Specification Sheet

Part Number: 133-03488



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple configurations to mount to a variety of surfaces

Releaseable to allow for maintenance

Conduit Clamps, Size 6, Bundling Clip Size 9 mm, PP, Black, 3000/pkg

Article Number 133-03488

Type CDC6BC9

Color Black (BK)

Quantity Per carton

Product Description
The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters.

Short Description
Conduit Clamps, Size 6, Bundling Clip Size 9 mm, PP, Black, 3000/pkg

Global Part Name
CDC6BC9-PP-BK

Length L (Imperial)	1.41
Length L (Metric)	35.7
Offset Length (Imperial)	0.48
Offset Length (Metric)	12.2
Fixation Method	Bundling Clip
Width W (Imperial)	0.9
Width W (Metric)	22.5
Bundle Diameter Max (Imperial)	0.35
Bundle Diameter Max (Metric)	9.0
Height H (Imperial)	1.73
Height H (Metric)	43.9
Diameter D (Imperial)	0.31
Diameter D (Metric)	8.0
Material	Polypropylene (PP)
Material Shortcut	PP

Flammability	UL 94 HB
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)