

Specification Sheet

Part Number: 150-55610



Fir tree mounts are equipped with a friction tab that will hold the tie in the mount, allowing them to be preassembled prior to installation.

Fir Tree design provides low extraction and high extraction force.

1-Piece Cable Tie with Fir Tree Mount with Disc, 4.3"L, 0.19 - 0.20" Mounting Hole, PA66, Black, 500/pkg

Article Number	150-55610
----------------	-----------

Type	T18RDP5
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. This is sold as an assembly with the cable tie.
---------------------	---

Short Description	1-Piece Cable Tie with Fir Tree Mount with Disc, 4.3"L, 0.19 - 0.20" Mounting Hole, PA66, Black, 500/pkg
-------------------	--

Global Part Name	T18RDP5-PA66-BK
------------------	-----------------

Minimum Tensile Strength (Imperial)	18
Minimum Tensile Strength (Metric)	80
Length L (Imperial)	4.3
Length L (Metric)	110.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.1
Width W (Metric)	2.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	0.79
Bundle Diameter Max (Metric)	20.0
Thickness T (Imperial)	0.043

Thickness T (Metric)	1.1
Panel Thickness Min (Imperial)	0.12
Panel Thickness Max (Imperial)	0.16
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	4.0
Mounting Hole Diameter D (Imperial)	0.19 - 0.2 "
Mounting Hole Diameter D (Metric)	4.9 - 5.1 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.2
Mounting Hole Diameter D Max (Metric)	5.1
Disc Diameter (Metric)	13.0
Disc Diameter (Imperial)	0.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)