

Specification Sheet

Part Number: 150-92600

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications

Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges



HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers

Connector Clip with Edge Clip, EC6, PA66HIRHS; Black, 1000/pkg

Article Number	150-92600
Type	CCEC6
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton connector clips, for oval holes, are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times.
Short Description	Connector Clip with Edge Clip, EC6, PA66HIRHS; Black, 1000/pkg

Global Part Name	CCEC6-PA66HIRHS-BK
Length L (Imperial)	0.94
Length L (Metric)	24.0
Fixation Method	Edge Clip
Variant	1.0 - 3.0 mm Edge
Width W (Imperial)	0.41
Width W (Metric)	10.4
Height H (Imperial)	0.59
Height H (Metric)	15.0
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)