

Specification Sheet

Part Number: 151-00758



Suitable for applications with minimal space.

CTAM has 4-way entry design for use in line or at 90° angle to cable run.

CTAM mounts are available in different sizes and materials.

Cable Tie Anchor Mount, 0.20" Hole Dia, 0.20" Max Tie Width, PEEK, Beige, 100/pkg

Article Number	151-00758
Type	CTAM2
Color	Beige (BGE)
Quantity Per	pack
Product Description	Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.
Short Description	Cable Tie Anchor Mount, 0.20" Hole Dia, 0.20" Max Tie Width, PEEK, Beige, 100/pkg
Global Part Name	CTAM2-PEEK-BGE

Length L (Imperial)	0.81
Length L (Metric)	20.5
Fixation Method	Screw Mount
Width W (Imperial)	0.4
Width W (Metric)	10.2
Cable Ties	T18 - T50
Height H (Imperial)	0.22
Height H (Metric)	5.5
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.2 "
Mounting Hole Diameter D (Metric)	5.1 mm
Mounting Hole Diameter D Max (Metric)	5.1
Material	Polyetheretherketone (PEEK)
Material Shortcut	PEEK

Flammability	UL 94 V-0
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-67°F to +464°F (-55°C to +240°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)