

Specification Sheet

Part Number: 151-00837



The 316 grade stainless steel offers excellent resistance to salt spray, corrosion, weather and chemicals.

Secures with a single screw for quick installation.

Stainless steel is nonflammable, offering added safety in regulated applications.

Stainless Steel Tie Mount, 0.16" Hole Dia, 0.39" Max Tie Width, Grade 316 SST, ML, 100/pkg

Article Number	151-00837
Type	SSPC4
Color	Metal (ML)
Quantity Per	pack
Product Description	Stainless steel P-mounts provide a robust and extremely durable mounting solution for a wide range of applications. With a 10 mm slot width and either a 4 mm, 5 mm or 6 mm panel hole, this two-way mount can be installed quickly and easily with a single screw or bolt, providing excellent performance and a high pull force. Designed for use with MBTS(-S), MBTH(-S) and MBTSFC stainless steel ties, or 18 through 120 pound nylon cable ties to provide stability when securing bundles.
Short Description	Stainless Steel Tie Mount, 0.16" Hole Dia, 0.39" Max Tie Width, Grade 316 SST, ML, 100/pkg

Global Part Name	SSPC4-SS316L-ML
Length L (Imperial)	0.91
Length L (Metric)	23.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.40
Width W (Metric)	10.2
Cable Ties	MBTS(-S) and MBTH(-S) stainless steel ties
Height H (Imperial)	0.18
Height H (Metric)	4.5
Cable Tie Width Max (Imperial)	0.39
Cable Tie Width Max (Metric)	10.0
Mounting Hole Diameter D (Imperial)	0.16 "
Mounting Hole Diameter D (Metric)	4.2 mm
Mounting Hole Diameter D Max (Metric)	4.2
Material	Stainless Steel (SS316L)

Material Shortcut	SS316L
Flammability	Non-burning
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	7326908695

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com