

Specification Sheet

Part Number: 151-01122



Separates bundles to help prevent chafing and wear.

Single bundles can be mounted on top of the mount, or two bundles can be separated using the two side saddles; giving the mount versatility.

Low profile design allows mount to be placed in areas where space is limited.

Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA66HIRHSUV, Black, 500/pkg

Article Number	151-01122
----------------	-----------

Type	LPM25
------	-------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Low Profile Mounts secure bundles close to mounting surfaces, making them ideal for applications where bundle mounting space is limited. These are secured with a .25" mechanical fastener, and have a counter bore for easy access with a socket which can be torqued up to 100 in/lbs. The mount accommodates cable ties up to .5" in width.
---------------------	--

Short Description	Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA66HIRHSUV, Black, 500/pkg
-------------------	---

Global Part Name	LPM25-PA66HIRHSUV-BK
------------------	----------------------

Length L (Imperial)	1.8
Length L (Metric)	45.1
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.98
Width W (Metric)	24.9
Cable Ties	T50 - T250
Height H (Imperial)	0.66
Height H (Metric)	16.7
Cable Tie Width Max (Imperial)	0.53
Cable Tie Width Max (Metric)	13.5
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.7 mm
Mounting Hole Diameter D Max (Metric)	6.7
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)