

Specification Sheet

Part Number: 151-01397

Connector clip design to meet USCAR EWCAP-005-7 clip slot specifications, assuring compliance.

Meets installation and extraction requirements of SAE/USCAR-2, delivering easy insertion with reliable performance.



Long fir tree designed for use in thicker panels up to 9.5 mm.

Oval fir tree prevents rotation in 9x17 mm holes.

Connector Clip with Oval Fir Tree, 9.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 2000/carton

Article Number	151-01397
----------------	-----------

Type	CC20
------	------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips are designed with various fixing point designs, to accommodate the many connectors out in the market. This specific connector clip is designed for a commonly used automotive connector. The width and the height of the fixation point creates minimal rattle when secured. The innovative design of the fir tree creates an interface with four different size holes that are common in the automotive industry. The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.
---------------------	---

Short Description	Connector Clip with Oval Fir Tree, 9.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 2000/carton
Global Part Name	CC20-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	35
Minimum Tensile Strength (Metric)	155
Length L (Imperial)	1.00
Length L (Metric)	25.5
Fixation Method	Fir Tree for oval holes
Variant	9.0 x 17.0 mm
Width W (Imperial)	0.80
Width W (Metric)	20.3
Height H (Imperial)	1.03
Height H (Metric)	26.1
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.37
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	9.5

Mounting Hole Diameter D (Imperial)	0.35 x 0.67 "
Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
Mounting Hole Diameter D Min (Imperial)	0.35
Mounting Hole Diameter D Max (Imperial)	0.35
Mounting Hole Diameter D Max (Metric)	9.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000

Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)