

Specification Sheet

Part Number: 151-02098



Mount and tie combination makes it easy to service bundles in the field.

Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.

Eliminates the needs for multiple sized fix diameter clamps.

High Torque Mount, 0.327" Mounting Hole Dia, 114.0 lb/ft Max Torque, PA66HIRHSUV, Black, 100/pkg

Article Number	151-02098
----------------	-----------

Type	HDM320
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The high-torque mount is designed for use with power-assisted impact wrenches and is molded with a heavy bushing to withstand the forces required to tighten grade 8 bolts. The arched H-profile of the saddle surface allows for a broad surface contact with the bundle, minimizing pinching and crushing of the bundles, and adjusts to a wide variety of bundle diameters when used with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.
---------------------	---

Short Description	High Torque Mount, 0.327" Mounting Hole Dia, 114.0 lb/ft Max Torque, PA66HIRHSUV, Black, 100/pkg
-------------------	--

Global Part Name	HDM320-PA66HIRHSUV-BK
------------------	-----------------------

Length L (Imperial)	1.85
---------------------	------

Length L (Metric)	47.0
-------------------	------

Fixation Method	Screw Mounting and Rivet
-----------------	--------------------------

Width W (Imperial)	1.0
--------------------	-----

Width W (Metric)	25.0
------------------	------

Height H (Imperial)	0.81
---------------------	------

Height H (Metric)	20.7
-------------------	------

Cable Tie Width Max (Imperial)	0.5
--------------------------------	-----

Cable Tie Width Max (Metric)	12.7
------------------------------	------

Mounting Hole Diameter D (Imperial)	0.33 "
-------------------------------------	--------

Mounting Hole Diameter D (Metric)	8.31 mm
-----------------------------------	---------

Mounting Hole Diameter D Max (Metric)	8.31
---------------------------------------	------

Stud Diameter (Metric)	8.3 mm
------------------------	--------

Stud Diamater (Imperial)	0.33
--------------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Maximum Torque (kgf-cm)	1576.0
Maximum Torque (lbf-ft)	114.0
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.