

Specification Sheet

Part Number: 151-02218



The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.

Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.

Disc around the fir tree eliminates potential debris and water to enter the panel hole.

LOC Locking Clamp, 10–14 mm Bundle Dia with FT9X12 Fir Tree, PA66HIRHSUV, Black, 100/pkg

Article Number	151-02218
----------------	-----------

Type	LOC1014FT9x12
------	---------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Locking Omega Clip creates a full and secure lock completely around a wire bundle ranging from 5-25 mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by utilizing a round or oval hole.
---------------------	--

Short Description	LOC Locking Clamp, 10–14 mm Bundle Dia with FT9X12 Fir Tree, PA66HIRHSUV, Black, 100/pkg
-------------------	--

Global Part Name	LOC1014FT9x12-PA66HIRHSUV-BK
------------------	------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	1.37
---------------------	------

Length L (Metric)	35.0
-------------------	------

Fixation Method	Fir Tree for oval holes
-----------------	-------------------------

Width W (Imperial)	0.47
--------------------	------

Width W (Metric)	12.0
------------------	------

Bundle Diameter Min (Imperial)	0.39
--------------------------------	------

Bundle Diameter Min (Metric)	10.0
------------------------------	------

Bundle Diameter Max (Imperial)	0.55
--------------------------------	------

Bundle Diameter Max (Metric)	14.0
------------------------------	------

Cable Ties	T50R
------------	------

Height H (Imperial)	2.31
---------------------	------

Height H (Metric)	58.57
-------------------	-------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.35 x 0.47 " 0.35 x 0.55 "
Mounting Hole Diameter D (Metric)	9.0 x 12.0 mm 9.0 x 14.0 mm
Mounting Hole Diameter D Min (Imperial)	0.35
Mounting Hole Diameter D Max (Imperial)	0.55
Mounting Hole Diameter D Max (Metric)	14.0
Disc Diameter (Metric)	23.63
Disc Diameter (Imperial)	0.93
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com