

Specification Sheet

Part Number: 151-02459



Connector clip design to meet USCAR EWCAP-005-11 clip slot specifications.

Meets installation and extraction requirements of SAE/USCAR-2.

Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength in a 5mm hole and M6 threaded hole.

USCAR Connector Clip with Round Fir Tree, 11mm, 5.0 mm Dia and M6 Threaded Hole, PA66HIRHSUV, Black, 5000/ctn

Article Number	151-02459
----------------	-----------

Type	CC11FTM6
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	USCAR Connector Clip with Round Fir Tree, 11mm, 5.0 mm Dia and M6 Threaded Hole, PA66HIRHSUV, Black, 5000/ctn
-------------------	---

Global Part Name	CC11FTM6-PA66HIRHSUV-BK
------------------	-------------------------

Length L (Imperial)	0.98
---------------------	------

Length L (Metric)	24.9
-------------------	------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Variant	M6 Threaded Hole
---------	------------------

Width W (Imperial)	0.622
--------------------	-------

Width W (Metric)	15.8
------------------	------

Height H (Imperial)	0.814
---------------------	-------

Height H (Metric)	20.7
-------------------	------

Panel Thickness Min (Imperial)	0.05
--------------------------------	------

Panel Thickness Max (Imperial)	0.18
--------------------------------	------

Panel Thickness Min (Metric)	1.3
------------------------------	-----

Panel Thickness Max (Metric)	4.5
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24
-------------------------------------	------

Mounting Hole Diameter D (Metric)	M6
-----------------------------------	----

Mounting Hole Diameter D Min (Imperial)	0.256
---	-------

Mounting Hole Diameter D Max (Imperial)	0.276
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	17.5
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5008
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)