

Specification Sheet

Part Number: 151-02949

Easy to install, remove and reposition with just a quarter-turn – no tools necessary.

Multi-directional cable tie slot allows for routing a bundle parallel to or perpendicular to the frame.

Low profile is ideal for cramped spaces.



Designed to fit an 80/20 profile with a T-slot of 8 mm (0.32") and external dimensions of 40 mm (1.5").

Aluminum Frame Mount for 40mm or 1.5" Frame, 4.0 - 4.8mm Panel Thickness, PA66MP+, Blue, 100/bg

Article Number

151-02949

Type

MCAFLM40-1

Color

Blue (BU)

Quantity Per

pack

Product Description

Aluminum frame mounts can be used with 20, 30 or 40 mm square frames from the major aluminum frame manufacturers. As there is no need to screw them in place, these mounts offer maximum ease of use and fast installation. The mounts contain metal particles for detection in processing plants where the potential for contamination is undesirable.

Short Description	Aluminum Frame Mount for 40mm or 1.5" Frame, 4.0 - 4.8mm Panel Thickness, PA66MP+, Blue, 100/bg
Global Part Name	MCAFLM40-1-PA66MD-BU
Length L (Imperial)	1.10
Length L (Metric)	28.0
Fixation Method	Profile rail
Width W (Imperial)	0.83
Width W (Metric)	21
Cable Ties	T18 - T50
Height H (Imperial)	0.80
Height H (Metric)	20.2
Panel Thickness Min (Imperial)	0.16
Panel Thickness Max (Imperial)	0.19
Panel Thickness Min (Metric)	4.0
Panel Thickness Max (Metric)	4.8

Material	Polyamide 6.6, metal detectable (PA66MD)
Material Shortcut	PA66MD
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com