

Specification Sheet

Part Number: 151-03568

Smaller footprint for applications where space is constrained.

Easily attaches to existing bolts or studs, eliminating the need for additional hardware.

Cover/stopper inside the clamp prevents stud from touching the cable bundle, minimizing chafing and protecting bundle from damage.

One-piece ratchet closure design allows for easy installation during pre- or final assembly.

Clamp interior is designed to guide and center bundles to reduce pinching.



M10 Stud Mount Ratchet Clamp, 1.42 - 2.0" Bundle Dia, PA66HIRHSUV, Black, 150/bg

Article Number	151-03568
Type	CMRCDSMM10
Color	Black (BK)
Quantity Per	pack

Product Description	The Stud Mount Ratchet Clamp offers versatility when managing wires, cables and hoses. It is especially convenient for locations with space constraints or where offset mounting options are not ideal. Easily attaches to existing studs or bolts without the need for additional hardware. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. Release feature allows easy and nondestructive removal or addition of cables simply by inserting a flat-head screwdriver. In this way, the clamp can be reused without removing it from the mounting surface.
Short Description	M10 Stud Mount Ratchet Clamp, 1.42 - 2.0" Bundle Dia, PA66HIRHSUV, Black, 150/bg
Global Part Name	CMRCDSMM10-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	250
Minimum Tensile Strength (Metric)	1112
Length L (Imperial)	5.89
Length L (Metric)	149.7
Fixation Method	Stud Mount
Width W (Imperial)	1.38
Width W (Metric)	35.1
Bundle Diameter Min (Imperial)	1.42
Bundle Diameter Min (Metric)	36.1
Bundle Diameter Max (Imperial)	2

Bundle Diameter Max (Metric)	50.8
Height H (Imperial)	1.20
Height H (Metric)	30.4
Stud Diameter (Metric)	M10
Stud Diamater (Imperial)	0.394
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	150
Package Quantity (Metric)	150
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)