

## Specification Sheet

Part Number: 151-03648



No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.

Magnetic Clamp, 0.50" Dia, Neodymium Magnet/POM/ST, 15lb Pull Force, Black, 100/bag

Article Number

151-03648

Type

MAGCLMP15L

Color

Black (BK)

Quantity Per

pack

Product Description

Magnetic clamps route bundles by securing to steel surfaces without the need for a mounting hole. Simply enclose the wire bundle in the clamp, close the locking clip, and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic clamps are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

|                                |                                                                                     |
|--------------------------------|-------------------------------------------------------------------------------------|
| Short Description              | Magnetic Clamp, 0.50" Dia, Neodymium Magnet/POM/ST, 15lb Pull Force, Black, 100/bag |
| Global Part Name               | MAGCLMP15L-NDFEB45M/POM/ST-BK                                                       |
| Fixation Method                | Magnet                                                                              |
| Width W (Imperial)             | 0.60                                                                                |
| Width W (Metric)               | 15.2                                                                                |
| Bundle Diameter Max (Imperial) | 0.5                                                                                 |
| Bundle Diameter Max (Metric)   | 12.7                                                                                |
| Height H (Imperial)            | 0.85                                                                                |
| Height H (Metric)              | 21.5                                                                                |
| Diameter D (Imperial)          | 0.91                                                                                |
| Diameter D (Metric)            | 23.2                                                                                |
| Material                       | Neodymium alloy 45M (NDFEB45M) Polyacetal (POM) Steel (ST)                          |
| Material Shortcut              | ST POM NDFEB45M                                                                     |
| Halogen Free                   | Yes                                                                                 |

|                              |                                  |
|------------------------------|----------------------------------|
| UV Resistant (Yes/No)        | No                               |
| Use Conditions               | For Indoor Use Only              |
| Plenum Rating                | AH-2                             |
| Operating Temperature        | -40°F to +176°F (-40°C to +80°C) |
| Reach Compliant (Article 33) | Yes                              |
| ROHS Compliant               | Yes                              |
| Package Quantity (Imperial)  | 100                              |
| Package Quantity (Metric)    | 100                              |
| Customs Number               | 8505110070                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com