

Specification Sheet

Part Number: 151-03655



No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.

Magnetic J-Hook 3/4" Dia Hook, Top Mount, Neodymium Magnet/Steel, 90lb Pull Force, 10/box

Article Number

151-03655

Type

MAGJH90TXS

Color

Metal (ML)

Quantity Per

pack

Product Description

Magnetic J-hooks route cables by securing to steel surfaces without the need for a mounting hole. Simply hang cables within the J-hook and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic J-hooks are ideal for supporting communication and data cables. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Short Description	Magnetic J-Hook 3/4" Dia Hook, Top Mount, Neodymium Magnet/Steel, 90lb Pull Force, 10/box
Global Part Name	MAGJH90TXS-NDFEB45M/ST-ML
Fixation Method	Magnet
Width W (Imperial)	0.88
Width W (Metric)	22.5
Height H (Imperial)	4.95
Height H (Metric)	125.8
Depth D (Imperial)	0.85
Depth D (Metric)	21.6
Diameter D (Imperial)	1.57
Diameter D (Metric)	40.0
Material	Steel (ST) Neodymium alloy 45M (NDFEB45M)
Material Shortcut	ST NDFEB45M
Halogen Free	Yes

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)