

Specification Sheet

Part Number: 151-03976

One-piece ratchet closure design allows for easy installation during pre- or final assembly.

Accommodates a range of diameters from 4-8 mm, reducing part inventory.

Round fir tree mounting option means no additional fastener is needed and provides low push-in effort while maintaining high pull-out resistance.

Clamp interior is designed to guide and center bundle to reduce pinching.

Easy-release feature allows for quick adjustments and maintenance.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.



Mini Ratchet P-Clamp, 0.15 - 0.31" Bundle Dia., FT6.5, PA66HIRHSUV, Black, 100/bg

Article Number	151-03976
----------------	-----------

Type	4-8RCFT6.5
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Mini Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The clamp size and design make it an ideal P-clamp replacement for securing sensor wires, brake lines or other wires. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This release feature allows the clamp to be reused without removing or replacing any bolts or screws.
Short Description	Mini Ratchet P-Clamp, 0.15 - 0.31" Bundle Dia., FT6.5, PA66HIRHSUV, Black, 100/bg
Global Part Name	4-8RCFT6.5-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	223
Length L (Imperial)	2.66
Length L (Metric)	67.7
Fixation Method	Fir tree for round holes
Width W (Imperial)	0.69
Width W (Metric)	17.5
Bundle Diameter Min (Imperial)	0.15
Bundle Diameter Min (Metric)	3.81
Bundle Diameter Max (Imperial)	0.31

Bundle Diameter Max (Metric)	7.874
Mounting Hole Diameter D (Imperial)	0.24 - 0.27
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Centers (Imperial)	0.98
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100

Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)