

Specification Sheet

Part Number: 151-04647



Fine-pitch ratchet provides controlled grip for a range of bundle sizes with one part.

Fully enclosed clamp prevents crushing and fallout.

Release latch with simple twist of screwdriver simplifies bundle maintenance.

ATI-specific stainless steel mounting clip designed for severe weather and single-axis tracker movement.

Ratchet O-Clamp for ATI, 0.73 - 0.89 " Bundle Dia., PA66HIRHSUV + 3/4 Hard SS, Black, 200/ctn

Article Number	151-04647
Type	ROC18.5-22.5ATI2
Color	Black (BK)
Quantity Per	box
Product Description	The Ratchet O-Clamp for Array Technologies attaches easily to ATI torque tubes thanks to a custom-designed clip. It offers one-handed, toolless simplicity and size versatility for managing wires and cables on solar modules. The robust design and solar-optimized materials make it ideal for heavy duty, outdoor applications. The one-piece adjustable clamp can be closed by hand to the desired diameter, replacing multiple sizes for single-diameter fasteners.
Short Description	Ratchet O-Clamp for ATI, 0.73 - 0.89 " Bundle Dia., PA66HIRHSUV + 3/4 Hard SS, Black, 200/ctn

Global Part Name	ROC18.5-22.5ATI2-PA66HIRHSUV/SS304-BK
------------------	---------------------------------------

Minimum Tensile Strength (Imperial)	100
-------------------------------------	-----

Minimum Tensile Strength (Metric)	445
-----------------------------------	-----

Length L (Imperial)	1.5
---------------------	-----

Length L (Metric)	37
-------------------	----

Fixation Method	Connector Clip
-----------------	----------------

Width W (Imperial)	1.7
--------------------	-----

Width W (Metric)	42.5
------------------	------

Bundle Diameter Min (Imperial)	0.73
--------------------------------	------

Bundle Diameter Min (Metric)	18.5
------------------------------	------

Bundle Diameter Max (Imperial)	0.89
--------------------------------	------

Bundle Diameter Max (Metric)	22.5
------------------------------	------

Height H (Imperial)	1.3
---------------------	-----

Height H (Metric)	33
-------------------	----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Stainless Steel (SS304)
Material Shortcut	SS304 PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com