

Specification Sheet

Part Number: DSWS50HSK2



H-profile of the saddles allows for broad surface contact with the bundle, which minimizes pinching and crushing of the bundle.

Swivels in 360-degree motion to accommodate any area.

Accommodates T50–T250 ties to handle both light-duty and heavy-duty applications.

Dual Swivel Saddle Spacer for T50-T250, Bundle Diameter 0.625 - 6", Black, PA66HS, 50/pkg

Article Number	151-06502
Type	DSWS5
Color	Black (BK)
Quantity Per	pack
Product Description	These saddle spacers are installed between two bundles (such as wires, cables, hoses, tubing, conduit, etc.) to separate and prevent chafing and wear. The mounts can be easily rotated by hand, allowing the bundles to be crossed and rotated at any angle. Cable ties, which secure the bundles, are used with the mounts. The dual swivel saddle spacers accommodate cable ties up to 1/2" wide.
Short Description	Dual Swivel Saddle Spacer for T50-T250, Bundle Diameter 0.625 - 6", Black, PA66HS, 50/pkg

Global Part Name	DSWS5-PA66HS/PA46-BK
Length L (Imperial)	1.60
Length L (Metric)	40.6
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	0.63
Bundle Diameter Min (Metric)	16.0
Bundle Diameter Max (Imperial)	5.98
Bundle Diameter Max (Metric)	152.0
Cable Ties	T50 - T250
Height H (Imperial)	0.9
Height H (Metric)	23.6
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Material	Polyamide 4.6 (PA46) Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HS PA46
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Minimum Extraction Force (Imperial)	250.0
Minimum Extraction Force (Metric)	1112
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)