

Specification Sheet

Part Number: 151-10920



2- or 4-way entry options for the Q-Tie, offering flexibility and stability

Designed for use with 18- through 120-pound cable ties to provide stability when securing bundles.

Secures with a single screw, providing quick installation.

Q Tie Mount, M4 Screw, 0.83 x 0.38 x 0.26", For Q18 - Q50 ties, PA66, Natural, 100/bg

Article Number	151-10920
----------------	-----------

Type	CTQM5
------	-------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Q-Series mounting bases are designed to work exclusively with the Q-Tie® cable tie series. This mounting component can be secured with screws. The Q-Mount allows either a two- or four-way entry for the Q-Tie, providing a quick and simple insertion into the mount. Once in place, the Q-Tie will not slip out, even in vertical mounting applications.
---------------------	---

Short Description	Q Tie Mount, M4 Screw, 0.83 x 0.38 x 0.26", For Q18 - Q50 ties, PA66, Natural, 100/bg
-------------------	---

Global Part Name	CTQM5-PA66-NA
------------------	---------------

Length L (Imperial)	0.83
Length L (Metric)	21.0
Fixation Method	Screw Mount
Width W (Imperial)	0.38
Width W (Metric)	9.5
Cable Ties	Q-Ties
Height H (Imperial)	0.26
Height H (Metric)	6.7
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.175
Mounting Hole Diameter D (Metric)	4.5 mm
Mounting Hole Diameter D Max (Metric)	4.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 1565 UL ANSI/UL 62275 UL ANSI/UL 746B
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)