

Specification Sheet

Part Number: CTAP110C2



Mount provides a "stand-off" for perpendicular bundles.

Secures with a single screw providing quick installation.

Cable Tie Anchor Mount, 0.20 x.75" Hole Dia, 0.20" Max Tie Width, PA66, White, 100/pkg

Article Number	151-30100
----------------	-----------

Type	CTAP1
------	-------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton cable tie anchor plates are designed as a "stand-off" mount for perpendicular wire bundles. These mounts offer an elongated mounting hole for easier alignment of wire bundles. The mounts are installed quick and easy by securing a single screw.
---------------------	---

Short Description	Cable Tie Anchor Mount, 0.20 x.75" Hole Dia, 0.20" Max Tie Width, PA66, White, 100/pkg
-------------------	--

Global Part Name	CTAP1-PA66-WH
------------------	---------------

Length L (Imperial)	1.34
Length L (Metric)	34.0
Fixation Method	Screw Mount
Width W (Imperial)	0.5
Width W (Metric)	12.7
Cable Ties	T18 - T50
Height H (Imperial)	.15
Height H (Metric)	3.80
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.2 x 0.75
Mounting Hole Diameter D (Metric)	5.0 x 19.0 mm
Mounting Hole Diameter D Max (Metric)	19.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)