

Specification Sheet

Part Number: CTM110M4



KR/CTM series are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Cable Tie Anchor Mount, 0.58 x .37", 0.19" Hole Dia, 0.2" Max Tie Width, PA66, White, 1000/pkg

| | |
|---------------------|---|
| Article Number | 151-30406 |
| Type | CTM1 |
| Color | White (WH) |
| Quantity Per | pack |
| Product Description | Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width. |
| Short Description | Cable Tie Anchor Mount, 0.58 x .37", 0.19" Hole Dia, 0.2" Max Tie Width, PA66, White, 1000/pkg |
| Global Part Name | CTM1-PA66-WH |

| | |
|---------------------------------------|----------------------|
| Length L (Imperial) | 0.58 |
| Length L (Metric) | 14.7 |
| Fixation Method | Screw Mount |
| Width W (Imperial) | 0.37 |
| Width W (Metric) | 9.4 |
| Cable Ties | T18 - T50 |
| Height H (Imperial) | .27 |
| Height H (Metric) | 6.90 |
| Cable Tie Width Max (Imperial) | 0.2 |
| Cable Tie Width Max (Metric) | 5.0 |
| Mounting Hole Diameter D (Imperial) | 0.19 |
| Mounting Hole Diameter D (Metric) | 4.8 mm |
| Mounting Hole Diameter D Max (Metric) | 4.8 |
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |

| | |
|-------------------------------|----------------------------------|
| Flammability | UL 94 V-2 |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor Use Only |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL 62275 |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity (Imperial) | 1000 |
| Package Quantity (Metric) | 1000 |
| Customs Number | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)