

Specification Sheet

Part Number: IMP2.5W1.7510H4

Identification Marker Plates can be marked with a permanent pen, printed labels or hot stamped for a wide variety of labeling options.

Any size bundle diameter can be marked because it is only dependent upon the length of the cable tie selected, provided the cable tie width does not exceed .29".



The marker plates are stamped from nylon, making them a durable and long term method of identification.

The mounting holes are positioned to allow the marker to be mounted as a flag, tag or wrapped around the cable or bundle for a wide variety of installed positions.

Identification Marker Plate, 2.5" x 1.75", Nylon, White, 500/pkg

Article Number 151-00242

Type IMP2.5W1.75

Color White (WH)

Quantity Per pack

Product Description Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.

Short Description	Identification Marker Plate, 2.5" x 1.75", Nylon, White, 500/pkg
Global Part Name	IMP2.5W1.75-PA66-WH
Length L (Metric)	63.5
Fixation Method	Others
Identification Plate Position	attached to bundle
Variant	Other
Width W (Imperial)	2.5
Width W (Metric)	63.5
Height H (Imperial)	1.75
Height H (Metric)	44.45
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)