

## Specification Sheet

Part Number: CTAP110M4



Mount provides a "stand-off" for perpendicular bundles.

Secures with a single screw providing quick installation.

Cable Tie Anchor Mount, 0.20 x.75" Hole Dia, 0.20" Max Tie Width, PA66, White, 1000/pkg

|                |           |
|----------------|-----------|
| Article Number | 151-00288 |
|----------------|-----------|

|      |       |
|------|-------|
| Type | CTAP1 |
|------|-------|

|       |            |
|-------|------------|
| Color | White (WH) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                     |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton cable tie anchor plates are designed as a "stand-off" mount for perpendicular wire bundles. These mounts offer an elongated mounting hole for easier alignment of wire bundles. The mounts are installed quick and easy by securing a single screw. |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                         |
|-------------------|-----------------------------------------------------------------------------------------|
| Short Description | Cable Tie Anchor Mount, 0.20 x.75" Hole Dia, 0.20" Max Tie Width, PA66, White, 1000/pkg |
|-------------------|-----------------------------------------------------------------------------------------|

|                  |               |
|------------------|---------------|
| Global Part Name | CTAP1-PA66-WH |
|------------------|---------------|

|                                       |                      |
|---------------------------------------|----------------------|
| Length L (Imperial)                   | 1.34                 |
| Length L (Metric)                     | 34.0                 |
| Fixation Method                       | Screw Mount          |
| Width W (Imperial)                    | 0.5                  |
| Width W (Metric)                      | 12.7                 |
| Cable Ties                            | T18 - T50            |
| Height H (Imperial)                   | .15                  |
| Height H (Metric)                     | 3.80                 |
| Cable Tie Width Max (Imperial)        | 0.2                  |
| Cable Tie Width Max (Metric)          | 5.0                  |
| Mounting Hole Diameter D (Imperial)   | 0.2 x 0.75 "         |
| Mounting Hole Diameter D (Metric)     | 5.0 x 19.0 mm        |
| Mounting Hole Diameter D Max (Metric) | 19.0                 |
| Material                              | Polyamide 6.6 (PA66) |
| Material Shortcut                     | PA66                 |

|                               |                                  |
|-------------------------------|----------------------------------|
| Flammability                  | UL 94 V-2                        |
| UV Resistant (Yes/No)         | No                               |
| Use Conditions                | For Indoor Use Only              |
| Operating Temperature         | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)  | Yes                              |
| ROHS Compliant                | Yes                              |
| Certification/Specification   | UL                               |
| UL Recognized (US)            | Yes                              |
| UL Recognized (US and Canada) | Yes                              |
| Package Quantity (Imperial)   | 1000                             |
| Package Quantity (Metric)     | 1000                             |
| Customs Number                | 3926909988                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com