

## Specification Sheet

Part Number: 151-00430

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Cips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.



Connector Clip, with Edge Clip, Panel Thickness 1.5-4.0mm, PA66HIRHS, Black, 500/pkg

Article Number 151-00430

Type EC43

Color Black (BK)

Quantity Per pack

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Connector Clip, with Edge Clip, Panel Thickness 1.5-4.0mm, PA66HIRHS, Black, 500/pkg

Global Part Name

EC43-PA66HIRHS-BK

Length L (Imperial) 0.95

Length L (Metric) 24.0

Fixation Method Edge Clip

Width W (Imperial) 0.53

Width W (Metric) 13.4

Height H (Metric) 18.0

Panel Thickness Min (Imperial) 0.06

Panel Thickness Max (Imperial) 0.16

Panel Thickness Min (Metric) 1.5

Panel Thickness Max (Metric) 4.0

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No) No

**Use Conditions****For Indoor and Outdoor Use**

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

RoHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)