

## Specification Sheet

Part Number: HDM190HIRH4



Mount and tie combination makes it easy to service bundles in the field.

Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.

Eliminates the needs for multiple sized fix diameter clamps.

Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.1875", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 500/pkg

Article Number 151-00436

Type HDM19

Color Black (BK)

Quantity Per pack

Product Description These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Short Description Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.1875", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 500/pkg

Global Part Name HDM19-PA66HIRHSUV-BK

|                                       |                          |
|---------------------------------------|--------------------------|
| Length L (Imperial)                   | 1.43                     |
| Length L (Metric)                     | 36.3                     |
| Fixation Method                       | Screw Mounting and Rivet |
| Width W (Imperial)                    | 0.76                     |
| Width W (Metric)                      | 19.3                     |
| Height H (Imperial)                   | 0.66                     |
| Height H (Metric)                     | 16.7                     |
| Cable Tie Width Max (Imperial)        | 0.50                     |
| Cable Tie Width Max (Metric)          | 12.7                     |
| Mounting Hole Diameter D (Imperial)   | 0.19 "                   |
| Mounting Hole Diameter D (Metric)     | 4.7 mm                   |
| Mounting Hole Diameter D Max (Metric) | 4.76                     |
| Stud Diameter (Metric)                | 4.8 mm                   |
| Stud Diamater (Imperial)              | 0.19                     |

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| Material                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut            | PA66HIRHSUV                                                              |
| Flammability                 | UL 94 HB                                                                 |
| UV Resistant (Yes/No)        | Yes                                                                      |
| Use Conditions               | For Indoor and Outdoor Use                                               |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                        |
| Maximum Torque (kgf-cm)      | 132.5                                                                    |
| Maximum Torque (lbf-ft)      | 9.583                                                                    |
| Reach Compliant (Article 33) | Yes                                                                      |
| ROHS Compliant               | Yes                                                                      |
| Package Quantity (Imperial)  | 500                                                                      |
| Package Quantity (Metric)    | 500                                                                      |
| Customs Number               | 3926909988                                                               |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com