

Specification Sheet

Part Number: RB14L4



Simple snap in design allows for quick and easy installation or removal of cables.

Rubber based adhesive allows for a permanent bond to most surfaces.

RB Adhesive Cable Clamp, 0.55" Max. Bundle Dia, PA66, Natural, 200/pkg

Article Number	151-00506
----------------	-----------

Type	RB14
------	------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	The RB Adhesive cable clamps are designed with an easy snap in feature allowing simple installation or removal of cables, pipes or hoses. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes.
---------------------	---

Short Description	RB Adhesive Cable Clamp, 0.55" Max. Bundle Dia, PA66, Natural, 200/pkg
-------------------	--

Global Part Name	RB14-PA66-NA
------------------	--------------

Length L (Imperial)	1.3
Length L (Metric)	33.2
Fixation Method	Pasting / Stick
Variant	Closed
Width W (Imperial)	1.1
Width W (Metric)	27.4
Bundle Diameter Max (Imperial)	0.55
Bundle Diameter Max (Metric)	14.0
Height H (Imperial)	0.63
Height H (Metric)	16.0
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	14
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam

Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com