


Specification Sheet

Part Number: 151-00651



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Fir Tree, 1.5" Long, 0.7 - 18.0mm Panel Thickness, PA66HIRHS, Natural, 2000/box

Article Number	151-00651
----------------	-----------

Type	TC6FT6LG
------	----------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
---------------------	---

Short Description	Bundling Clip with Fir Tree, 1.5" Long, 0.7 - 18.0mm Panel Thickness, PA66HIRHS, Natural, 2000/box
-------------------	--

Global Part Name	TC6FT6LG-PA66HIRHS-NA
------------------	-----------------------

Length L (Imperial)	1.5
Length L (Metric)	38.1
Fixation Method	Fir Tree
Width W (Imperial)	0.5
Width W (Metric)	12.0
Height H (Imperial)	1.0
Height H (Metric)	26.60
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.71
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	18.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.8

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)