

Specification Sheet

Part Number: 151-00775

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.



Connector Clip with Round Arrowhead, 1.7-2.3 mm Panel Thick., 6.3-6.7 mm Hole Dia, PA66HIRHS, Black, 5000/box

Article Number	151-00775
----------------	-----------

Type	CCSFT6.5
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton connector clips for oval holes are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The arrowhead locks firmly into place when inserted into the hole palpably and ensures a secure attachment at all times.
---------------------	---

Short Description	Connector Clip with Round Arrowhead, 1.7-2.3 mm Panel Thick., 6.3-6.7 mm Hole Dia, PA66HIRHS, Black, 5000/box
-------------------	---

Global Part Name	CCSFT6.5-PA66HIRHS-BK
------------------	-----------------------

Length L (Imperial)	0.9
---------------------	-----

Length L (Metric)	23.0
-------------------	------

Fixation Method	Arrowhead
-----------------	-----------

Width W (Metric)	16.1
------------------	------

Height H (Imperial)	0.48
---------------------	------

Height H (Metric)	12.1
-------------------	------

Panel Thickness Min (Imperial)	0.07
--------------------------------	------

Panel Thickness Max (Imperial)	0.09
--------------------------------	------

Panel Thickness Min (Metric)	1.7
------------------------------	-----

Panel Thickness Max (Metric)	2.3
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.25 - 0.26 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.25
---	------

Mounting Hole Diameter D Max (Imperial)	0.26
---	------

Mounting Hole Diameter D Max (Metric)	6.7
---------------------------------------	-----

Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)