

Specification Sheet

Part Number: 151-00783



Clip includes an internal rib that spans the inside of the bracket to fit securely into the profile of the tubing to prevent lateral movement and slipping of the tubing.

Extended fir tree allows for a wide range of panel thicknesses.

Fir tree design provides low insertion forces and high extraction forces.

Side Convoluted Tubing Clip, Max Bundle Diameter .6", PA66HIRHS, Black, 5000/pkg

Article Number	151-00783
----------------	-----------

Type	CTCFT6
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Convoluted Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface. Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.
---------------------	--

Short Description	Side Convoluted Tubing Clip, Max Bundle Diameter .6", PA66HIRHS, Black, 5000/pkg
-------------------	--

Global Part Name	CTCFT6-PA66HIRHS-BK
------------------	---------------------

Length L (Imperial)	0.43
Length L (Metric)	11.0
Fixation Method	Fir Tree
Variant	Clips
Width W (Imperial)	0.43
Width W (Metric)	11.0
Bundle Diameter Min (Imperial)	0.43
Bundle Diameter Min (Metric)	11.0
Bundle Diameter Max (Imperial)	0.59
Bundle Diameter Max (Metric)	15.0
Height H (Imperial)	0.73
Height H (Metric)	18.5
Nominal Diameter (Imperial)	1.56
Nominal Diameter (Metric)	15.0
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.18

Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	4.5
Mounting Hole Diameter D (Imperial)	0.25 - 0.26 "
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5003

Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)