

Specification Sheet

Part Number: 151-00925

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.



An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip with Oval Fir Tree, 0.6-6.0mm Panel Thick, 6.2-13.0mm Hole Dia, PA66HIRHSUV, Black, 5000/ctn

Article Number	151-00925
Type	CCOVAL
Color	Black (BK)
Quantity Per	pack
Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
Short Description	Connector Clip with Oval Fir Tree, 0.6-6.0mm Panel Thick, 6.2-13.0mm Hole Dia, PA66HIRHSUV, Black, 5000/ctn

Global Part Name	CCOVAL-PA66HIRHSUV-BK
Length L (Imperial)	1.16
Length L (Metric)	29.34
Fixation Method	Fir Tree for oval holes
Variant	6.2 x 12.2 mm 6.5 x 12.5 mm 6.5 x 13.0 mm 7.0 x 12.0 mm
Width W (Imperial)	0.69
Width W (Metric)	17.63
Height H (Imperial)	0.79
Height H (Metric)	19.98
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.26 x 0.50 " 0.26 x 0.51 " 0.28 x 0.47 " 0.24 x 0.48 "
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm 6.5 x 12.5 mm 6.5 x 13.0 mm 6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial) 0.24

Mounting Hole Diameter D Max (Metric) 6.2

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)