

Specification Sheet

Part Number: 151-00927



Pre-drilled holes allows for easy installation by hand.

Cable can be removed and reinstalled without removing the clip, providing multiple use options.

Made of PA66HIRHSUV material for withstanding extreme conditions.

Fir Tree C-Clip, 0.24 - 0.30" Bundle Dia, 0.03 - 0.25" Panel, 0.26" Mount Hole, PA66HIRHSUV, Black, 100/pkg

Article Number	151-00927
----------------	-----------

Type	SC6.6
------	-------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The C Clip with fir tree mount is ideal for panels with pre-drilled holes. Easy installation by hand eliminates the need for any tools. Once installed, the cable simply snaps into the clip. The cable can be removed and reinstalled without removing the clip. Made from PA66HIRHSUV material, the clip offers increased flexibility along with heat resistance and UV stability.
---------------------	--

Short Description	Fir Tree C-Clip, 0.24 - 0.30" Bundle Dia, 0.03 - 0.25" Panel, 0.26" Mount Hole, PA66HIRHSUV, Black, 100/pkg
-------------------	---

Global Part Name	SC6.6-PA66HIRHSUV-BK
------------------	----------------------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	0.72
--------------------	------

Width W (Metric)	18.26
------------------	-------

Bundle Diameter Min (Imperial)	0.24
--------------------------------	------

Bundle Diameter Min (Metric)	6.0
------------------------------	-----

Bundle Diameter Max (Imperial)	0.3
--------------------------------	-----

Bundle Diameter Max (Metric)	7.6
------------------------------	-----

Height H (Imperial)	1.32
---------------------	------

Height H (Metric)	33.43
-------------------	-------

Panel Thickness Min (Imperial)	0.03
--------------------------------	------

Panel Thickness Max (Imperial)	0.25
--------------------------------	------

Panel Thickness Min (Metric)	0.7
------------------------------	-----

Panel Thickness Max (Metric)	6.35
------------------------------	------

Mounting Hole Diameter D (Imperial)	0.26 "
-------------------------------------	--------

Mounting Hole Diameter D (Metric)	6.6 mm
-----------------------------------	--------

Mounting Hole Diameter D Max (Metric)	6.6
Disc Diameter (Metric)	18.55
Disc Diameter (Imperial)	0.73
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)