

Specification Sheet

Part Number: 151-00994

The 90-degree configuration of this mini channel creates a solution for routing a wire harness around a corner.

Design allows the mini channel to be used with a wide range of panel thicknesses and hole diameters.



Disc prevents rattling in high-vibration applications and protects against leakage and debris.

Mini Channel, 1.2" Long, 90° Angle, Arrowhead, PA66HIRHSUV, Black, 4000/ctn

Article Number	151-00994
Type	BC90AH
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's Bundling Clips create a solution that allows the harness to be routed around a corner, and fixated into the panel at this location.
Short Description	Mini Channel, 1.2" Long, 90° Angle, Arrowhead, PA66HIRHSUV, Black, 4000/ctn
Global Part Name	BC90AH-PA66HIRHSUV-BK

Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	Arrowhead
Width W (Imperial)	0.06
Width W (Metric)	1.5
Height H (Imperial)	0.98
Height H (Metric)	24.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.07
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	1.8
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.8

Disc Diameter (Metric)	21.34
Disc Diameter (Imperial)	0.84
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)