

Specification Sheet

Part Number: 151-01020



KR/CTM series are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Metal Content Cable Tie Anchor Mount, 0.98"x.57", 0.2" Hole Dia, 0.33" Max Tie Width, PA66MP+, Blue, 100/pkg

Article Number	151-01020
Type	MCKR8G5-5
Color	Blue (BU)
Quantity Per	pack
Product Description	Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.
Short Description	Metal Content Cable Tie Anchor Mount, 0.98"x.57", 0.2" Hole Dia, 0.33" Max Tie Width, PA66MP+, Blue, 100/pkg
Global Part Name	MCKR8G5-5-PA66MD-BU

Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	Screw Mount
Width W (Imperial)	0.57
Width W (Metric)	14.5
Cable Ties	MCT18 - MCT120
Height H (Imperial)	0.47
Height H (Metric)	12.0
Cable Tie Width Max (Imperial)	0.33
Cable Tie Width Max (Metric)	8.3
Mounting Hole Diameter D (Imperial)	0.20 "
Mounting Hole Diameter D (Metric)	5.1 mm
Mounting Hole Diameter D Max (Metric)	5.1
Material	Polyamide 6.6, metal detectable (PA66MD)
Material Shortcut	PA66MD

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)