

Specification Sheet

Part Number: 151-01022



The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.

Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.

Disc around the fir tree eliminates potential debris and water to enter the panel hole.

LOC Locking Clamp, 15-19 mm, with 6.5 mm Fir Tree, PA66HIRHSUV, Black, 2000/ctn

Article Number	151-01022
----------------	-----------

Type	LOC15-19FT6LG
------	---------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Locking Omega Clamp fully encircles and securely locks around wire bundles ranging from 15-19 mm. Its uniquely engineered fir tree holds tightly in hole sizes from 6.1 mm to 7 mm. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.
---------------------	---

Short Description	LOC Locking Clamp, 15-19 mm, with 6.5 mm Fir Tree, PA66HIRHSUV, Black, 2000/ctn
-------------------	---

Global Part Name	LOC15-19FT6LG-PA66HIRHSUV-BK
------------------	------------------------------

Length L (Imperial)	1.24
---------------------	------

Length L (Metric)	31.6
-------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	0.47
--------------------	------

Width W (Metric)	12.0
------------------	------

Bundle Diameter Min (Imperial)	0.59
--------------------------------	------

Bundle Diameter Min (Metric)	15.0
------------------------------	------

Bundle Diameter Max (Imperial)	0.75
--------------------------------	------

Bundle Diameter Max (Metric)	19.0
------------------------------	------

Height H (Imperial)	1.87
---------------------	------

Height H (Metric)	47.5
-------------------	------

Depth D (Imperial)	0.47
--------------------	------

Depth D (Metric)	12.0
------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.32
--------------------------------	------

Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	8.25
Mounting Hole Diameter D (Imperial)	0.24 - 0.28 " 0.24 - 0.26 " (HEXAGONAL)
Mounting Hole Diameter D (Metric)	6.1 - 6.6 mm (hexagonal) 6.1 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)