

Specification Sheet

Part Number: 151-01119



Connector clips with bracket provide a simple and easy method for mounting connectors in a variety of applications

Detailed designs includes clamp for mounting on edges

Connector Clip with Bracket, 2.80" Long, PA66HIRHSUV, Black, 1000/box

Article Number	151-01119
----------------	-----------

Type	BCBRKTSB5
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton Tape-On Connector Clips are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.
---------------------	---

Short Description	Connector Clip with Bracket, 2.80" Long, PA66HIRHSUV, Black, 1000/box
-------------------	---

Global Part Name	BCBRKTSB5-PA66HIRHSUV-BK
Length L (Imperial)	2.8
Length L (Metric)	71.0
Width W (Imperial)	1.97
Width W (Metric)	50.0
Height H (Imperial)	0.69
Height H (Metric)	17.65
Stud Diameter (Metric)	5.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)