

Specification Sheet


Part Number: 151-01169

Designed for use with MCT18 - MCT30 cable ties to provide stability when securing bundles.

Simple to install with a screw or rivet.

Metal content dispersed throughout mount ensures identification by metal detectors and X-ray machines.

Industry standard blue color assists with visual detection and reduces the risk of contamination.



Metal Content Cable Tie Screw Mount, 0.75 x 0.75", 0.14" Max Tie Width, 0.12" Hole Dia, PA66MP, Blue, 6000/ctn

Article Number	151-01169
Type	MCMB3
Color	Blue (BU)
Quantity Per	pack
Product Description	The MCMB3 mounts are for use with HellermannTyton MCT18 - MCT30 Series cable ties to provide stability when securing bundles. The Metal Content Mount is specifically designed for the food, beverage and pharmaceutical processing industries to meet the safety standards set by the Hazardous Analysis of Critical Control Point (HACCP). The mount is nylon-based with metal content dispersed throughout allowing for the part to be identified by metal detectors or X-ray inspections, reducing the risk of contamination.

Short Description	Metal Content Cable Tie Screw Mount, 0.75 x 0.75", 0.14" Max Tie Width, 0.12" Hole Dia, PA66MP, Blue, 6000/ctn
Global Part Name	MCMB3-PA66MD-BU
Length L (Imperial)	0.75
Length L (Metric)	19.0
Fixation Method	Screw Mount
Width W (Imperial)	0.75
Width W (Metric)	19.0
Cable Ties	MCT18 - MCT30
Height H (Imperial)	0.17
Height H (Metric)	4.3
Cable Tie Width Max (Imperial)	0.14
Cable Tie Width Max (Metric)	3.5
Mounting Hole Diameter D (Imperial)	0.12 "
Mounting Hole Diameter D (Metric)	3.1 mm
Mounting Hole Diameter D Max (Metric)	3.1
Mounting Hole Centers (Imperial)	0.52

Material	Polyamide 6.6, metal detectable (PA66MD)
Material Shortcut	PA66MD
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	6000
Package Quantity (Metric)	6000
Customs Number	3926909988

